


Ninox SWIR 640

High resolution, low noise, cooled, digital VIS-SWIR camera
640 x 512 • Cooled to -20°C • <50e in high gain •



Key Features and Benefits

The best performing SWIR camera in the World!

- **Cooled VIS-SWIR technology**
Cooled to -20°C. Enables low dark current and longer exposure
- **15µm x 15µm pixel pitch**
Enables highest resolution VIS-SWIR image
- **<50e in high gain**
Enables highest VIS-SWIR detection limit
- **Ultra high intrascene dynamic range - 70dB**
Enables simultaneous capture of bright & dark portions of a scene
- **On-board intelligent 3 point NUC**
Enables highest quality images

Resolution	640 x 512
Frame Rate	Up to 120Hz
Cameralink	14 bit
Wavelength Range	VIS-SWIR
Dark Current	<1,500 e/p/s

Specification for Ninox SWIR 640

Sensor	SCD
Sensor Type	InGaAs PIN-Photodiode
Active Pixel	640 x 512
Pixel Pitch	15µm x 15µm
Active Area	9.6mm x 7.68mm
Spectral response ¹	0.4µm to 1.7µm
Noise (RMS)	<195 electrons Low Gain, <50 electrons High Gain
Quantum Efficiency	Peak >85% (>73% @ 1.064µm, 78% @ 1.55µm)
Pixel Well Depth	650Ke Low Gain, 12Ke High Gain
Pixel Operability	>99.5%
Dark Current	<1,500e/p/s @ -20°C
Digital Output Format	14 bit CameraLink (Base Configuration)
Exposure time	10µs to 26.8sec or 1/frame rate Low Gain 100µs to 26.8sec or 1/frame rate High Gain
Shutter mode	Global shutter
Frame Rate	up to 120Hz
Optical Interface	C-mount (selection of SWIR lens available)
Camera Setup / Control	CameraLink
Dynamic Range	14 bit
Trigger interface	Trigger IN and OUT - TTL compatible
Power supply	12V DC ±10%
TE Cooling	to -35°C Delta
Image Correction	3 point NUC (offset, Gain & Dark Current) + pixel correction
Functions controlled by serial communication	Exposure, intelligent AGC, Non Uniformity Correction, Gamma, Pk/Av, TEC, ROI
Camera Power Consumption ²	< 4W with TEC OFF (Typical)
Operating Case Temperature ³	-20°C to +55°C
Storage Temperature	-30°C to +60°C
Dimensions & Weight	90mm x 64mm x 123mm / 916g

Raptor Photonics Limited reserves the right to change this document at any time without notice and disclaims liability for editorial, pictorial or typographical errors.

Ordering Information

Camera

NINOX 640 VIS-SWIR digital camera	NX1.7-VS-CL-640
NINOX Power Supply Cable	RPL-HR4-K
Chiller	RPL-AMS-OASIS160 ⁴
Chiller Tubing	RPL-WTUBE-NINOX ⁵
Water cooling system	RPL-WCUC-WCS

Optional Accessories

EPIX(R) base CL card	RPL-EPIX-EB1
EPIX(R) base notebook CL card	RPL-EPIX-ECB1-34
EPIX(R) base notebook CL card	RPL-EPIX-ECB1-54
EPIX(R) XCAP STD software	RPL-XCAP-STD
CameraLink Cable, 2m ⁶	RPL-CL-CBL-2M
Optical SWIR lenses ⁷	RPL-xx-xxxx

Note 1: Optional filters available: Low, High or bandpass

Note 2: Measured @ 30°C

Note 3: Extended Operating Temperature range on request

Note 4: This includes the chiller and the liquid

Note 5: This includes the tube + connectors

Note 6: Longer CL cable available

Note 7: Please consult us to check our range of lenses




Edificio Antalia, Albasanz 16. 28037 Madrid
+34 91 567 97 00 | alavaingenieros.com | alava@grupoalava.com
Madrid | Barcelona | Zaragoza | Lisboa | Lima | Quito | Texas

Demo is available on request.
Pricing AOR subject to volumes.

Detailed technical drawings
can be downloaded at
www.raptorphotonics.com

Quantum Efficiency



Applications

- Astronomy
- Beam Profiling
- Hyperspectral Imaging
- Semiconductor Inspection
- Solar Cell Inspection
- Thermography
- Microscopy
- Art Inspection

Document #: INNINOX 1.7-VS-CL-640 0116R1



Willowbank Business Park
Larne, Co Antrim
BT40 2SF,
Northern Ireland

T: +44(0)2828 270 141
E: sales@raptorphotonics.com
www.raptorphotonics.com

