


Strain Gage Installation Kit **SGK-01**

Description

The Strain Gage Installation Kit allows a fast, easy and reproducible way of installing the fibre optic Strain Gages SG-01 to various surfaces. Installation of the optical gages happens using a patented methodology which makes use of a specially designed mounting tool called a sensor pad. After installation, the pad is removed from the sensor so that it does not interfere with the strain measurement during operation. This also makes that the pad can be reused for the installation of other sensors afterwards.

The used adhesive is UV-curable, which makes that installation is fast and easily controllable. Curing of the adhesive happens in two steps: (1) a fast pre-cure (typically 30 seconds with a 100 W mercury lamp) through the sensor pad and (2) a longer final cure after removal of the sensor pad to fully cure the adhesive (typically 5 to 10 minutes with a 100 W mercury lamp).



Features

- Fast, easy and reproducible installation of the SG-01 optical Strain Gages thanks to the sensor pad and a UV-curable adhesive. For an experienced worker, installation takes roughly 10 to 20 minutes.
- Applicable on various metallic and composite surfaces. Performances were validated on steel, stainless steel, aluminum, inconel, titanium, glass composite and carbon composite.
- Excellent fatigue resistance (tested up to 2 million cycles) and negligible transverse sensitivity.

Applications

The Strain Gage Installation Kit can be used to install the optical strain gages SG-01 on various surfaces so that stress and strain analysis of the structures to which they are attached can be performed.

Standard specifications

The Installation Kit contains all the necessary materials and tools for proper installation of the gages. It also includes a detailed instruction manual which guides the user through all the necessary steps during installation. The items contained in the Kit are listed in the table below.

Item	Quantity
Instruction manual	1
Data sheets and safety forms	1
Sensor pads (re-usable)	2
UV-curable adhesive (1 oz. bottle)	1
Abrasive paper (1 m ribbon)	1
Box with cleaning tissues (90 pieces)	1
Bottle of cleaning agent (85 g)	2
Teflon patches	20
Rectangular glass piece	1
Rapid Adhesive component A	1
Rapid Adhesive component B	2
Mixing cups	9
Spoons	2
Wooden stirring sticks	50
Tweezers	1
Scalpel	1
Mechanical protection (90 ml tube)	1
Fibre Optic Strain Gages SG-01*	20

* With mixed wavelengths from 1530 nm, 1535 nm, ... to 1560 nm.

The optical Strain Gages SG-01 which are properly installed by means of the Installation Kit exhibit the following characteristics:

Parameter	Unit	Value
Total sensor length	mm	45
Temperature operating range	°C	-50 to 70 (long term) 70 to 90 (short term; < 1 h)
Thermal stability	µε / h	≤ -0.026 @ 70 °C ≤ -5 @ 90 °C
Strain range (tension / compression)	%	0.5
Gage factor (S_ϵ)	µε ⁻¹	7.77 x 10 ⁻⁷ (typical)
Relative statistical error on S_ϵ	%	0.5
Temperature coefficient ¹ on S_ϵ	°C ⁻¹	2.7 10 ⁻⁴
Transverse strain sensitivity ²	-	< 2.1 10 ⁻³
Fatigue shift ³	µε / 10 ⁶ cycles	≤ 4

¹ The temperature coefficient of the gage factor S_ϵ expresses the relative variation of S_ϵ per degree Celsius.

² According to ASTM E 251-92. The transverse strain sensitivity is the ratio of the gage factor of a strain gage mounted perpendicular to a uniaxial strain field (transverse gage) to the gage factor of a similar gage mounted parallel to the same strain field (longitudinal gage).

³ The bonding during fatigue cycling was tested by mounting gages on unidirectional glass composite material that was strained from -0.24 % to +0.24 % up to 2 million cycles.

Optional Accessories

- UV-lamp

Ordering information

S	G	K	0	1
---	---	---	---	---

This product has been developed in the framework of a joint collaboration between the Belgian Science Policy and the Federal Public Service of Economy, SMEs, Independent Professions and Energy of Belgium.

FOS&S BVBA reserves the right to make changes without further notice to any products herein. FOS&S makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does FOS&S BVBA assume any liability arising out of the application or use of any product, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. Typical parameters that may be provided in FOS&S data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters must be validated for each customer application by customer's technical experts. FOS&S BVBA does not convey any license under its patent rights nor the rights of others. FOS&S BVBA products are not designed, intended, or authorized for use as components in systems intended to support or sustain life, or for any other application in which the failure of the FOS&S product could create a situation where personal injury or death may occur. Should Buyer purchase or use FOS&S products for any such unintended or unauthorized application, Buyer shall indemnify and hold FOS&S BVBA and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that FOS&S BVBA was negligent regarding the design or manufacture of the part.

FOS&S and the FOS&S logo are trademarks of FOS&S BVBA.
All other product or service names are the property of their respective owners.
FOS&S BVBA 2009. All rights reserved.